




Seal ring set D72 + O-rings

! The ability of the seal rings - to seal off and retain the product inside the product chamber depends on the unique surface geometry of both seal rings combined. To prolong the functional lifetime of the seal rings, please apply any type of food grade oil on the sealing faces before installing the mechanical seal. A worn and a new seal ring should not be mixed, therefore replace the seal rings in pair – as supplied.



690.0020 P180, P156

01	1020-0124	O-ring 88.00 x 2.50
02	600.0075	Seal ring D72S
03	1020-0100	O-ring 92.00 x 3.00
04	600.0072	Seal ring D72R
05	1020-0073	O-ring 89.50 x 3.00
06	1020-0123	O-ring 85.00 x 2.50