





Seal ring set D50 + O-rings

NOTE: The ability of the seal rings - to seal off and retain the product inside the product chamber depends on the unique surface geometry of both seal rings combined. To prolong the functional lifetime of the seal rings, please apply any type of food grade oil on the sealing faces before installing the mechanical seal. A worn and a new seal ring should not be mixed, therefore replace the seal rings in pair – as supplied.




690.0021 P105 / PRM 50 bar

01	1020-0042	O-ring 64.39 x 1.78
02	600.0052	Seal ring D50S
03	1020-0043	O-ring 67.60 x 2.40
04	600.0050	Seal ring D50R
05	1020-0040	O-ring 69.50 x 3.00
06	1020-0039	O-ring 66.40 x 1.78



690.0022 P125/P150 / PRM 120 bar

01	1020-0042	O-ring 64.39 x 1.78
02	600.0052	Seal ring D50S
03	1020-0058	O-ring 67.95 x 2.62
04	600.0050	Seal ring D50R
05	1020-0069	O-ring 69.52 x 2.62
06	1020-0039	O-ring 66.40 x 1.78



690.0023 Phase Inverter

01	1020-0042	O-ring 64.39 x 1.78
02	600.0052	Seal ring D50S
03	1020-0058	O-ring 67.95 x 2.62
04	600.0050	Seal ring D50R
05	1020-0040	O-ring 69.50 x 3.00
06	1020-0039	O-ring 66.40 x 1.78