




### Seal ring set D107 + O-rings

*! The ability of the seal rings - to seal off and retain the product inside the product chamber depends on the unique surface geometry of both seal rings combined. To prolong the functional lifetime of the seal rings, please apply any type of food grade oil on the sealing faces before installing the mechanical seal. A worn and a new seal ring should not be mixed, therefore replace the seal rings in pair – as supplied.*

Reconditioning of the seal faces: These seal rings are designed so that they offer a reconditioning allowance of 0.5mm on the thickness of the seal ring of each ring. Therefore, please do not discard the box in which you received the seal rings. Once the seal rings do no longer perform properly you should order new ones and send back to us the used ones for reconditioning.



P250

<b>01</b>	<b>600.0167</b>	<b>Face gasket D107 S</b>
02	600.0128	Seal ring D107 S
03	1020-0071	O-ring 126.60 x 3.53, (2x)
04	600.0127	Seal ring D107 R
<b>06</b>	<b>600.0166</b>	<b>Face gasket D107 R</b>