




Seal ring set D25 + O-rings

! The ability of the seal rings - to seal off and retain the product inside the product chamber depends on the unique surface geometry of both seal rings combined. To prolong the functional lifetime of the seal rings, please apply any type of food grade oil on the sealing faces before installing the mechanical seal. A worn and a new seal ring should not be mixed, therefore replace the seal rings in pair – as supplied.



690.0081 P57

01	1020-0203	O-ring 33.30 x 2.40
02	600.0330	Seal ring D25S
03	1020-0067	O-ring 37.77 x 2.62
04	600.0331	Seal ring D25R
05	1020-0219	O-ring 36.14 x 2.62
06	1020-0220	O-ring 31,60 x 2.40